





| REVISION HISTORY | | | |
|------------------|-----------|---------|-----------------|
| REV | DATE | BY | DESCRIPTION |
| B | 31MAR2017 | DMS/YGC | PRN: P2017-0751 |



| | | | |
|---|---|---------------------------------------|-------------------|
| R4-0-50114 | BRACKET | STAINLESS STEEL | PASSIVATE |
| PART NUMBER | TYPE OF COMPONENT | MATERIAL | FINISH |
| SURFACE AREA 7632.476mm ² | THIRD ANGLE PROJECTION | | |
| VOLUME 10214.198mm ³ | MILLIMETERS [IN] | | |
| | TOLERANCES UNLESS OTHERWISE NOTED | DESCRIPTION BRACKET , STRIKER , R4 | |
| | ALL DIMENSIONS WITHOUT TOLERANCES ARE FOR REFERENCE ONLY. | SIZE A4 | SYSTEM NX |
| PROPRIETARY ITEM EXCEPT FOR USES EXPRESSLY GRANTED IN WRITING, INFORMATION DISCLOSED HEREON IS CONFIDENTIAL AND ALL RIGHTS, PATENT AND OTHERWISE ARE RESERVED BY SOUTHCO, INC. | PER ASME Y14.5M-1994 | DWG NO. J-R4-0-50114 | DATE 19NOV2011 |
| | | SCALE 1:1 | SHEET 1 OF 1 |