

A complete set of Southco's magnetic catches consists of a positive fixed catch and a negative fixed or swivel catch. Follow steps 1 - 3 below to select a set of magnetic catches.

#### DESIGN CONSIDERATIONS

**Need to accommodate for manufacturing variability or door / panel sag?**

Swivel catches offer adjustability in angle and height.

**Limited space in your application?**

Fixed catches offer flush and low profile solutions.



#### 1 Select the Magnetic Catch Strength

Catch 1 Strength	Catch 2 Strength	Nominal Hold
Low	Low	50 N (11 lb)
Low	High	69 N (15 lb)
High	High	118 N (26 lb)

#### 2 Select a Positive Catch Style to fit your Application



Flush Fixed Catch



Proud Fixed Catch

Low Strength	M5-7P-41-8	M5-7P-42-8
High Strength	M5-7P-61-8	M5-7P-62-8

#### 3 Select a Negative Catch Style to fit your Application



Flush Fixed Catch



Proud Fixed Catch



Low Profile Swivel Catch



Adjustable Height Swivel Catch  
60-89 mm  
(2.36-3.5 in)



Adjustable Height Swivel Catch  
75-101 mm  
(2.95-3.98 in)



Adjustable Height Swivel Catch  
68.5-95 mm  
(2.7-3.74 in)

Low Strength	M5-7N-41-8	M5-7N-42-8	M5-7N-43-8	M5-7N-44-8	M5-7N-45-8	N/A
High Strength	M5-7N-61-8	M5-7N-62-8	M5-7N-63-8	N/A	N/A	M5-7N-65-8